





**SPECIFICATIONS**

Current Rating: 1 Amp  
 Insulation Resistance: 5000 Megohms Min.  
 Contact Resistance: 30 Milliohms Max.  
 Dielectric Strength: 600VAC Min.  
 Operating Temperature: -55°C To +105°C  
 Durability: 50 Cycles  
 Retention Force: 454g Min.  
 Contact: Copper Alloy  
 Housing: Thermoplastic, UL 94V-0  
 Contacts: 2x2~2x50



Recommended PCB Layout



**4UCON** 元化興業股份有限公司  
 4UCON TECHNOLOGY INC.

DRAWING No.		APPROVED BY		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE .X ±0.38 .XX ±0.25 ANG. ±5°
16846		MEI		
		BECKY		
		DRAWING BY		
		HZF		
SCALE	NONE	REV.	A0	UNIT mm

NO.	REV.	REVISIONS	CHK	DATE
△ A0		NEW RELEASE	BECKY	02/04/2005