

Mating receptical to be assembled as a set





Connector A Manfacturer - JST Part #s S2B-PH-K-S Plug entry view



Connector B Manfacturer - JST Part #s PHR-2 Crimp Pin Part # SPH-002T-P0.5S Or equivalent Wire Entry View **Scale 5.00**


Tolerances. Unless noted-0.0 +/-

0.00 +/-0.000 +/-


| Connector A Pin | Connector B Pin | Wire Type | | | | |
|-----------------|-----------------|------------------------|---------------------------|----------------------------------|--|--|
| 1 | 1 | Braided 24 AWG - Red | | JST_3-PIN_WITH_WIREOUTS | | |
| 2 | 2 | Braided 24 AWG - Black | IST 3-PIN | | | |
| | | | | | | |
| | | | | | | |
| | | Sheilding and cable | | | | |
| | | jacket type are not | Units In | Drawn by Spark Fun Electronics | | |
| | | of importance. | Utilis iti | Drawn by Spark I dif Electronics | | |
| | | | 20 Apr 10 | for Price Quote | | |
| | | | 20 Apr 10 for Price Quote | 101 The Quote | | |
| | | | Toloropoo I/ 0 125 | Drofton IIII Cools 1.25 | | |
| | | | Tolerance +/- 0.125 | Drafter HH Scale 1.25 | | |

Mating receptical to be assembled as a set





Connector A
Manfacturer - JST
Part #s S3B-PH-K-S... S5B-PH-K-S
Or equivalent
Plug entry view



Connector B
Manfacturer - JST
Part #s PHR-3...PHR-5
Crimp Pin Part # SPH-002T-P0.5S
Or equivalent
Wire Entry View
Scale 5.00

Tolerances, Unless noted-0.0 +/-

0.00 +/-0.000 +/-

| Connector A Pin | Connector B Pin | Wire Type | | <u>.</u> | |
|-----------------|-----------------|---|-------------------------|--------------------------------|--|
| 1 | 1 | Braided 24 AWG - Yellow | JST_3-PIN_WITH_WIREOUTS | | |
| 2 | 2 | Braided 24 AWG - Black | | | |
| 3 | 3 | Braided 24 AWG - Red | | | |
| 4 | 4 | Braided 24 AWG - Blue | | | |
| 5 | 5 | Braided 24 AWG - Green | | | |
| | | | Units in | Drawn by Spark Fun Electronics | |
| | | Sheilding and cable jacket type are not | 20 Apr 10 | for Price Quote | |
| | | of importance. | Tolerance +/- 0.125 | Drafter HH Scale 1.25 | |

| Set number | Part Numbers (Parts from JST or equivalent) | Notes | Page 3 / 3 | |
|------------|---|--|--|--|
| 1 | 1 x S2B-PH-K-S 1 x PHR-2 2 x SPH-002T-P0.5S 2 x Braided 24 AWG | Wire colors and order given on sheet 1 | | |
| 2 | 1 x S3B-PH-K-S 1 x PHR-3 3 x SPH-002T-P0.5S 3 x Braided 24 AWG | Wire colors and order given on sheet 2 (use yellow, black, & red wires) | | |
| 3 | 1 x S4B-PH-K-S 1 x PHR-4 4 x SPH-002T-P0.5S 4 x Braided 24 AWG | Wire colors and order given on sheet 2 (use yellow, black, red, and blue wires) | | |
| 4 | 1 x S5B-PH-K-S 1 x PHR-5 5 x SPH-002T-P0.5S 5 x Braided 24 AWG | Wire colors and order given on sheet 2 (use yellow, black, red, blue, and green wires) | | |
| | | | Tolerances, Unless noted- 0.0 +/- 0.000 +/- | |
| | | JST_3-PIN_WITH_WIREOUTS | | |
| | | Drawn by Spark Fun Electronics for | | |
| | | Drafter | Scale | |