

承 认 书

APPROVAL

SHEET

客 户
CUSTOMER SparkFun

品 名
DESCRIPTION USB A/F TO 2.54MM HOUSING

料 号
PART NO. PL-PM005

日 期
DATE 2010-10-06

客户承认栏 CUSTOMER APPROVAL

核准 APPROVED	审核 CHECKED	确认 ACCEPT

核准 APPROVED	审核 CHECKED	制定 DRAWN
		sevtev



DongGuan PengLian Electronics Co., Ltd

电话: 0769-38835098/38835094


传真: 0769-38835091

TEL: 0769-38835098/38835094

FAX: 0769-38835091

地 址: 东莞市长安镇厦岗第一工业区

Add: The 1st Industrial area, XiaGang Village , ChangAn Town, DongGuan City



USB A/F

2.54MM 1*4P


- NOTES:
1. ELECTRICAL TEST: 100% OPEN, SHORT & MIS WIRE TEST.
 2. CONTACT RESISTANCE: 2 ohm,
 3. INSULATOR RESISTANCE: 10M ohm.
 4. HIGH VOLTAGE: DC 300V 0.01sec.
 5. MUST BE ROHS COMPLIANT.

BOM PL-EF-04

8	HOUSING	2.54MM HOUSING 1*4P	1PCS
7	TERMINAL	2.54MM TERMINAL	4PCS
6	TUBE	∅4.0*15mm HEAT SHRINK TUBE BLACK	1PCS
5	SCREW	M3 SCREW NUT	2PCS
4	MOLDING	PVC 45P BLACK	7.3g/PCS
3	MOLDING	PE	1.5g/PCS
2	CONNECTOR	USB A/F 4P PIN GOLD PLATED SHELL NICKEL PLASTIC: WHITE	1PCS
1	CABLE	UL2725 28AWG (7/0.12TC) *1P (WHITE, GREEN) +28AWG (7/0.12TC) *2C (RED, BLACK) +AL+D (7/0.12TC) +B (64/0.12CCAM) JACKET PVC 60P BLACK OD=4.0 ± 0.1mm L=1830 ± 10mm	1PCS
NO.	NAME	SPECIFICATION	Q'TY

PIN WIRING

P1	RED	P2	4
1	WHITE	3	3
2	GREEN	2	2
3	BLACK	1	1
4			

		朋联电子有限公司 DongGuan Penglian Electronics Co., Ltd TEL: 076938835098/38835094 FAX: 076938835091	
TITLE		USB A/F TO 2.54MM HOUSING	
CUSTOMER		SparkFun	
CUSTOMER'S ITEM		PL-PM005	
SCALE	1:1	DRAWN BY	sevev
UNIT	mm	CHECKED BY	
REV.	A	APPROVED BY	
		DATE	2010-10-06
		DRAWING NO.	PL-SF-0002