



1	MCLR	AN9/RP15/CN11/RB15	26	RB15
2		AN10/RP14/CN12/RB14	25	RB14
3		AN11/RP13/CN13/RB13	24	RB13
4		AN12/RP12/CN14/RB12	23	RB12
5		PGEC2/TMS/RP11/CN15/RB11	22	TX0
6		PGED2/TDI/RP10/CN16/RB10	21	RXI
7				
8				
9	OSCI	TDO/SDA1/RP9/CN12/RB9	18	RB9
10	OSCO	TCK/SCL/RP8/CN22/RB8	17	RB8
11		INT0/RP7/CN23/RB7	16	RB7
12		PGEC3/ASCL1/RP6/CN24/RB6	15	RB6
13		PGED3/ASDA1/RP5/CN27/RB5	14	RB5
14		SOSCI/RP4/CN1/RB4	11	RB4
15		AN5/RP3/CN7/RB3	7	AN5
16		AN4/RP2/CN6/RB2	6	AN4
17		PGEC1/AN3/C2IN+/RP1/CN5/RB1	5	PGFC
18		PGED1/AN2/C2IN-/RP0/CN4/RB0	4	PGFD
19				
20				
21				
22				
23				
24				
25				
26				
27	AUSS	AN1/UREF-/CN2/RA1	3	AN1
28	AVDD	AN0/UREF+/CN2/RA0	2	AN0
29		SOSCO/T1CK/CN0/RA4	12	RA4
30				



⊗ ⊗	
TITLE: PIC24-Breakout-v12	SFE
Document Number:	REV:
Date: 8/21/2008 11:32:35 PM	Sheet: 1/1