


**NOTE:** The HantouchUSA Incoming Inspection Standard is part of this drawing. This quality and performance document can be viewed at: [www.hantouchUSA.com](http://www.hantouchUSA.com), under Incoming Inspection Standards.

**REMARK**

1. Glass Thk: 0.7mm
2. Film Type: Anti-Glare
3. Total Thk: 1.0±0.1mm
4. Linearity: ±1.8% or less
5. Transmittance: 80% or more
6. Resistance  
400<X<1200 ohm (Typ: 750 ohm)  
100<Y<700 ohm (Typ: 300 ohm)
7. Connector: FPC
8. General Tolerance : ±0.3mm


**CIRCUIT DIAGRAM**



**SIGNAL ASSIGNMENT**

Pin No	Signal
1	X1
2	Y2
3	X2
4	Y1

**Detail "AA" (Scale=3/1)**



REV.No.	REVISED	DATE	DRAWN	CHECKED	APPROVED
1		05.03.17	B. J. LEE		J. W. AHN
0	NEW DRAW	05.03.15	B. J. LEE		J. W. AHN

APPROVE	UNIT	mm	PROJECTION	DRAWING NO.	REV.
CHECK	SCALE	NONE		HT043A-NCOFD52-R	
DESIGN				DESCRIPTION	SHEET
DRAW				4.3 TOUCH PANEL	1/1