


4UCON 元化興業股份有限公司
4UCON TECHNOLOGY INC.

DRAWING No.		APPROVED BY		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
15882		MEI		
		CHECKED BY HZF		
		DRAWING BY LXX		X. ±0.25 X'. ±8"
SCALE	NONE	REV.	BO	.X ±0.15 .X' ±4"
				.XX ±0.10 .XX' ±2"
				UNIT mm

NO.	REV.	REVISIONS	CHK	DATE
△ BO		NEW RELEASE	HZF	09/09/2008

SPECIFICATION:

Current Rating:0.5A.
 Voltage Rating:250V AC/DC
 Dielectric Withstanding Voltage:AC 500V r.m.s.
 Insulation Resistance:1000 Megohm Min
 At DC 500V.
 Contact Resistance:100 Milliohms Max
 Operating Temperature:-20°c~60°c
 Contact Retention Force:3.0N Min./Per Contact
 Mating Force:9.8N Max
 Unmating Force:1.47N Min And 9.80N Max
 Housing:HI-Temp Plastic UL 94V-0 Rated.
 Contact:Copper Alloy(C5191H t=0.15mm).
 Grounding:Copper Alloy(C2680H t=0.15mm).
 Shell:Stainless Steel(SUS304 t=0.15mm).
 RoHS Compliant



Pin No.	
P1	DAT2
P2	CD\DAT3
P3	CMD
P4	VDD
P5	CLK
P6	VSS
P7	DAT0
P8	DAT1 ²

4UCON 元化興業股份有限公司
 4UCON TECHNOLOGY INC.

DRAWING No.

15882

APPROVED BY

MEI

CHECKED BY

HZF

DRAWING BY

LXX


UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

X. ±0.25 X'. ±8"
 .X ±0.15 .X' ±4"
 .XX ±0.10 .XX' ±2"

SCALE NONE

REV. BO

UNIT mm



NO.	REV.	BO	NEW RELEASE	HZF	09/09/2008
		REVISIONS		CHK	DATE