





SPECIFICATIONS
 Current Rating: 1.5 Amp
 Insulator Resistance: 1000 Megohms Min.
 Contact Resistance: 20 Milliohms Max.
 Dielectric Withstanding: AC 500V/Minute
 Operating Temperature: -40°C To +105°C
 Contact: Phosphor Bronze, Gold Flash Over All
 Insulator: Polyester, PA6T+30%GF, UL 94V-0



Recommended P.C.Board Hole Layout



4UCON 元化興業股份有限公司
 4UCON TECHNOLOGY INC.

DRAWING No.		APPROVED BY		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE .X ±0.38 .XX ±0.25 .XXX ±0.12			
00281		MEI					
		CHECKED BY					
		BECKY					
		DRAWING BY					
		HZF					
SCALE	NONE	REV.	B1	UNIT			
				mm			

NO.	REV.	REVISIONS	CHK	DATE
△ B1		Modify PA66 → PA6T	SHIN	02/06/2006
△ B0		NEW RELEASE	BECKY	09/30/2005