





**SPECIFICATIONS**

Current: 3A  
 Contact Resistance: 20 Milliohms Max.  
 Insulation Resistance: 1000 Megohms Min.  
 Withstanding Voltage: AC 1000V RMS  
 Operating Temperature: -55°C To +105°C  
 Housing: Thermoplastic UL94V-0  
 Contact: Copper Alloys



Recommended P.C.B Layout



**4UCON** 元化興業股份有限公司  
 4UCON TECHNOLOGY INC.

11029

APPROVED BY MEI  
 CHECKED BY HZF  
 DRAWING BY PEGA

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE  
 .X ±0.38  
 .XX ±0.25  
 ANG ±5°

SCALE NONE REV. A0

UNIT mm

NO.	REV.	DESCRIPTION	CHK	DATE
△ A0		NEW RELEASE	HZF	09/27/2006
		REVISIONS		