



Specifications:
 Material:
 Contact: Brass, Green
 Wire Guard: Stainless Steel
 Surface of Solder Tail: Tin plated
 Insulator Body(Housing): Polyamide(Glass filled)(UL94V-0)
 Electrical
 Voltage Rating: 150VAC
 Current Rating: 2Amps/way max
 Contact Resistance: 20 Milliohms(max)
 Insulation Resistance: 1000 Megohms min.
 Wire Range: 20-26AWG
 Mechanical:
 Operating Temperature: -55°C ~+105°C
 Test Temperature: 250°C, 5 Seconds Max.

4UCON 元化興業股份有限公司
 4UCON TECHNOLOGY INC.

DRAWING No.		APPROVED BY		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE .X ±0.30 .XX ±0.10 ANG. ±1°
11380		MEI		
		CHECKED BY		
		BECKY		
		DRAWING BY		
		HZF		
SCALE	NONE	REV.	A0	UNIT
				mm

NO.	REV.	REVISIONS	CHK	DATE
0	A0	NEW RELEASE	MEI	