


# 80W Switching Mode DC Power Supply

## 3-in-1 Power Supply

Three output ranges perform like 3 power supplies in one

### Features:

- Constant voltage or current
- 3 selectable ranges:
  - 0 to 16V/0 to 5A
  - 0 to 27V/0 to 3A
  - 0 to 36V/0 to 2.2A
- 4-Digit LED displays
- Front/Rear output terminals
- Remote sensing for accurate applied voltage at load point
- Compact slim tower housing is ideal for tight work bench
- Lightweight for easy portability
- Complete with AC Power cord



Current limited DC supply for electronic repair and calibration

Specifications			
Voltage Output (3 ranges)	0 to 16.4V	0 to 27.6V	0 to 36.8V
Current Output (3 ranges)	0 to 5.1A	0 to 3.1A	0 to 2.3A
Basic accuracy	±1%		
Ripple & Noise	<30mVpp		
Line Regulation	<4mV		
Load Regulation	<20mV		
Display	Dual 4-digit LED displays		
Power	90-264VAC; 47-63Hz		
Dimensions	13 x 5 x 2" (330 x 127 x 53.5mm)		
Weight	4.2lbs (1.9kg)		

### Ordering Information:

382260 .....80W Switching Mode DC Power Supply

