
µA7800 SERIES POSITIVE-VOLTAGE REGULATORS

SLVS056J - MAY 1976 - REVISED MAY 2003

- 3-Terminal Regulators
- Output Current up to 1.5 A
- Internal Thermal-Overload Protection



- High Power-Dissipation Capability
- Internal Short-Circuit Current Limiting
- Output Transistor Safe-Area Compensation

KTE PACKAGE (TOP VIEW)

description/ordering information

This series of fixed-voltage integrated-circuit voltage regulators is designed for a wide range of applications. These applications include on-card regulation for elimination of noise and distribution problems associated with single-point regulation. Each of these regulators can deliver up to 1.5 A of output current. The internal current-limiting and thermal-shutdown features of these regulators essentially make them immune to overload. In addition to use as fixed-voltage regulators, these devices can be used with external components to obtain adjustable output voltages and currents, and also can be used as the power-pass element in precision regulators.

Тј	VO(NOM) (V)	PACKAGE [†]		ORDERABLE PART NUMBER	TOP-SIDE MARKING
		POWER-FLEX (KTE)	Reel of 2000	μA7805CKTER	μA7805C
	5	TO-220 (KC)	Tube of 50	μA7805CKC	μA7805C
		TO-220, short shoulder (KCS)	Tube of 20	μA7805CKCS	μΑ7805C
		POWER-FLEX (KTE)	Reel of 2000	μA7808CKTER	μA7808C
	8	TO-220 (KC)	Tube of 50	μA7808CKC	μA7808C
		TO-220, short shoulder (KCS)	Tube of 20	μA7808CKCS	μΑ78080
	10	POWER-FLEX (KTE)	Reel of 2000	μA7810CKTER	μA7810C
0°C to 125°C	10	TO-220 (KC)	Tube of 50	μA7810CKC	μA7810C
0 0 10 125 0		POWER-FLEX (KTE)	Reel of 2000	μA7812CKTER	μA7812C
	12	TO-220 (KC)	Tube of 50	μA7812CKC	μA7812C
		TO-220, short shoulder (KCS)	Tube of 20	μA7812CKCS	μΑ/0120
		POWER-FLEX (KTE)	Reel of 2000	μA7815CKTER	μA7815C
	15	TO-220 (KC)	Tube of 50	μA7815CKC	
		TO-220, short shoulder (KCS)	Tube of 20	μA7815CKCS	μA7815C
	24	POWER-FLEX (KTE)	Reel of 2000	μA7824CKTER	μA7824C
	24	TO-220 (KC)	Tube of 50	μA7824CKC	μA7824C

ORDERING INFORMATION

[†] Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.


PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.



μA7800 SERIES POSITIVE-VOLTAGE REGULATORS

SLVS056J - MAY 1976 - REVISED MAY 2003

schematic



absolute maximum ratings over virtual junction temperature range (unless otherwise noted)[†]

Input voltage, V _I : μA7824C	0 V
All others	5 V
Operating virtual junction temperature, T _J 150	J∘C
Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds	J∘C
Storage temperature range, T _{stg} –65°C to 150)°C

[†] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

package thermal data (see Note 1)

PACKAGE	BOARD	ΟL ^θ	θJA
POWER-FLEX (KTE)	High K, JESD 51-5	3°C/W	23°C/W
TO-220 (KC/KCS)	High K, JESD 51-5	3°C/W	19°C/W

NOTE 1: Maximum power dissipation is a function of $T_J(max)$, θ_{JA} , and T_A . The maximum allowable power dissipation at any allowable ambient temperature is $P_D = (T_J(max) - T_A)/\theta_{JA}$. Operating at the absolute maximum T_J of 150°C can affect reliability.



SLVS056J - MAY 1976 - REVISED MAY 2003

recommended operating conditions

		MIN	MAX	UNIT
V _I Input voltage	μA7805C	7	25	
	μA7808C	10.5	25	
	μA7810C	12.5	28	v
	μA7812C	14.5	30	v
	μA7815C	17.5	30	
	μA7824C	27	38	
IO	Output current		1.5	А
ТJ	Operating virtual junction temperature	0	125	°C

electrical characteristics at specified virtual junction temperature, $V_I = 10 V$, $I_O = 500 mA$ (unless otherwise noted)

PARAMETER	TEST CONDITIONS		- +	μ Α7805C			
PARAMETER			т _J †	MIN	TYP	MAX	
Output voltogo	$I_O = 5 \text{ mA to 1 A}, V$	= 7 V to 20 V,	25°C	4.8	5	5.2	V
Output voltage	P _D ≤ 15 W		0°C to 125°C	4.75		5.25	v
Input voltage regulation	$V_I = 7 V \text{ to } 25 V$		25°C		3	100	mV
input voltage regulation	$V_{I} = 8 V$ to 12 V		25 C		1	50	mv
Ripple rejection	V _I = 8 V to 18 V, f =	= 120 Hz	0°C to 125°C	62	78		dB
Output voltage regulation	I _O = 5 mA to 1.5 A		25°C		15	100	mV
	I _O = 250 mA to 750 mA		25 C		5	50	IIIV
Output resistance	f = 1 kHz		0°C to 125°C		0.017		Ω
Temperature coefficient of output voltage	I _O = 5 mA		0°C to 125°C		-1.1		mV/°C
Output noise voltage	f = 10 Hz to 100 kHz		25°C		40		μV
Dropout voltage	I _O = 1 A		25°C		2		V
Bias current			25°C		4.2	8	mA
Diag gutternt shange	V _I = 7 V to 25 V I _O = 5 mA to 1 A					1.3	~ 1
Bias current change			0°C to 125°C	0.5		mA	
Short-circuit output current			25°C		750		mA
Peak output current			25°C		2.2		А



μΑ7800 SERIES POSITIVE-VOLTAGE REGULATORS

SLVS056J - MAY 1976 - REVISED MAY 2003

electrical characteristics at specified virtual junction temperature, $V_I = 14 V$, $I_O = 500 mA$ (unless otherwise noted)

PARAMETER	TEST CONDITIONS	- +	μ Α78	UNIT	
PARAMETER	TEST CONDITIONS	т _J †	MIN T	YP MAX	
O desta desta de	$I_{O} = 5 \text{ mA to 1 A}, \qquad V_{I} = 10.5 \text{ V to 2}$	23 V, 25°C	7.7	8 8.3	v
Output voltage	$P_{D} \le 15 W$	0°C to 125°C	7.6	8.4	Ň
	$V_{I} = 10.5 V$ to 25 V	25°C		6 160	mV
Input voltage regulation	V _I = 11 V to 17 V	25°C		2 80	mv
Ripple rejection	V _I = 11.5 V to 21.5 V, f = 120 Hz	0°C to 125°C	55	72	dB
	I _O = 5 mA to 1.5 A	0500		12 160	
Output voltage regulation $I_{O} = 250 \text{ mA to } 750 \text{ mA}$		25°C		4 80	mV
Output resistance	f = 1 kHz	0°C to 125°C	0.0	16	Ω
Temperature coefficient of output voltage	IO = 5 mA	0°C to 125°C	-	0.8	mV/°C
Output noise voltage	f = 10 Hz to 100 kHz	25°C		52	μV
Dropout voltage	I _O = 1 A	25°C		2	V
Bias current		25°C		4.3 8	mA
Disc surrent change	$V_{I} = 10.5 V \text{ to } 25 V$	0°C to 125°C		1	
Bias current change	$I_{O} = 5 \text{ mA to } 1 \text{ A}$	0°C to 125°C	0.5		mA
Short-circuit output current		25°C	2	50	mA
Peak output current		25°C		2.2	А

[†] Pulse-testing techniques maintain the junction temperature as close to the ambient temperature as possible. Thermal effects must be taken into account separately. All characteristics are measured with a 0.33-μF capacitor across the input and a 0.1-μF capacitor across the output.

electrical characteristics at specified virtual junction temperature, $V_I = 17 V$, $I_O = 500 mA$ (unless otherwise noted)

PARAMETER	TEST CONDITIONS		_ +	μ Α7810C			UNIT
PARAMETER			т _J †	MIN	TYP	MAX	
Output voltage	$I_{O} = 5 \text{ mA to } 1 \text{ A},$	V _I = 12.5 V to 25 V,	25°C	9.6	10	10.4	V
	P _D ≤ 15 W	-	0°C to 125°C	9.5	10	10.5	v
Input voltage regulation	V_{I} = 12.5 V to 28 V		25°C		7	200	mV
input voltage regulation	V _I = 14 V to 20 V		25 C		2	100	IIIV
Ripple rejection	V _I = 13 V to 23 V,	f = 120 Hz	0°C to 125°C	55	71		dB
	I _O = 5 mA to 1.5 A		0500		12	200	mV
Output voltage regulation	I _O = 250 mA to 750 mA		25°C		4	100	
Output resistance	f = 1 kHz		0°C to 125°C		0.018		Ω
Temperature coefficient of output voltage	I _O = 5 mA		0°C to 125°C		-1		mV/°C
Output noise voltage	f = 10 Hz to 100 kHz		25°C		70		μV
Dropout voltage	I _O = 1 A		25°C		2		V
Bias current			25°C		4.3	8	mA
Bias current change	VI = 12.5 V to 28 V		0°C to 125°C			1	mA
Blas current change	$I_{O} = 5 \text{ mA to } 1 \text{ A}$		0 C 10 125 C	0.5		mA	
Short-circuit output current			25°C		400		mA
Peak output current			25°C		2.2		А



$\mu \text{A7800 SERIES} \\ \text{POSITIVE-VOLTAGE REGULATORS} \\$

SLVS056J - MAY 1976 - REVISED MAY 2003

electrical characteristics at specified virtual junction temperature, V_I = 19 V, I_O = 500 mA (unless otherwise noted)

PARAMETER	TEST CONDITIONS		_ +	μ Α7812C			UNIT
PARAMETER			т _J †	MIN	TYP	MAX	
Output voltage	I _O = 5 mA to 1 A,	V _I = 14.5 V to 27 V,	25°C	11.5	12	12.5	V
	P _D ≤ 15 W		0°C to 125°C	11.4		12.6	v
Input voltage regulation	VI = 14.5 V to 30 V		25°C		10	240	mV
input voltage regulation	VI = 16 V to 22 V		25 C		3	120	IIIV
Ripple rejection	Vj = 15 V to 25 V,	f = 120 Hz	0°C to 125°C	55	71		dB
	I _O = 5 mA to 1.5 A		0500		12	240	mV
Output voltage regulation	I _O = 250 mA to 750 mA		25°C		4	120	mv
Output resistance	f = 1 kHz		0°C to 125°C		0.018		Ω
Temperature coefficient of output voltage	IO = 5 mA		0°C to 125°C		-1		mV/°C
Output noise voltage	f = 10 Hz to 100 kHz		25°C		75		μV
Dropout voltage	I _O = 1 A		25°C		2		V
Bias current			25°C		4.3	8	mA
Pice current change	V_{I} = 14.5 V to 30 V					1	mA
Bias current change	$I_{O} = 5 \text{ mA to } 1 \text{ A}$		0°C to 125°C	0.5		0.5	
Short-circuit output current			25°C		350		mA
Peak output current			25°C		2.2		А

[†] Pulse-testing techniques maintain the junction temperature as close to the ambient temperature as possible. Thermal effects must be taken into account separately. All characteristics are measured with a 0.33-μF capacitor across the input and a 0.1-μF capacitor across the output.

electrical characteristics at specified virtual junction temperature, $V_I = 23 V$, $I_O = 500 mA$ (unless otherwise noted)

PARAMETER	TEST CONDITIONS	_ +	μ Α7815C			UNIT
PARAMETER	TEST CONDITIONS	TJ‡	MIN	TYP	MAX	
Output voltage	$I_{O} = 5 \text{ mA to 1 A}, V_{I} = 17.5 \text{ V to 30 V}$	25°C	14.4	15	15.6	V
Output voltage	$P_{D} \le 15 W$	0°C to 125°C	14.25		15.75	v
	V _I = 17.5 V to 30 V	25°C		11	300	mV
Input voltage regulation	V _I = 20 V to 26 V	25°C		3	150	mv
Ripple rejection	$V_{I} = 18.5 V$ to 28.5 V, $f = 120 Hz$	0°C to 125°C	54	70		dB
	IO = 5 mA to 1.5 A	25°C		12	300	
Output voltage regulation	I _O = 250 mA to 750 mA	25°C		4 150		mV
Output resistance	f = 1 kHz	0°C to 125°C		0.019		Ω
Temperature coefficient of output voltage	I _O = 5 mA	0°C to 125°C		-1		mV/°C
Output noise voltage	f = 10 Hz to 100 kHz	25°C		90		μV
Dropout voltage	I _O = 1 A	25°C		2		V
Bias current		25°C		4.4	8	mA
Ripp ourrent chonge	VI = 17.5 V to 30 V	0°C to 125°C			1	mA
Bias current change	$I_{O} = 5 \text{ mA to } 1 \text{ A}$	0 0 10 125 0	0.5			
Short-circuit output current		25°C		230		mA
Peak output current		25°C		2.1		А



μΑ7800 SERIES POSITIVE-VOLTAGE REGULATORS

SLVS056J - MAY 1976 - REVISED MAY 2003

electrical characteristics at specified virtual junction temperature, $V_I = 33 V$, $I_O = 500 mA$ (unless otherwise noted)

	TEST CONDITIONS		- +	μ Α7824C			UNIT
PARAMETER			т _J †	MIN	ТҮР	MAX	UNIT
Output veltage	$I_{O} = 5 \text{ mA to } 1 \text{ A},$	V _I = 27 V to 38 V,	25°C	23	24	25	V
Output voltage	P _D ≤ 15 W		0°C to 125°C	22.8		25.2	v
	VI = 27 V to 38 V		25°C		18	480	mV
Input voltage regulation	VI = 30 V to 36 V		25.0		6	240	mv
Ripple rejection	V _I = 28 V to 38 V,	f = 120 Hz	0°C to 125°C	50	66		dB
	$I_{O} = 5 \text{ mA to } 1.5 \text{ A}$ $I_{O} = 250 \text{ mA to } 750 \text{ mA}$		0500		12	480	mV
Output voltage regulation			25°C		4	240	mv
Output resistance	f = 1 kHz		0°C to 125°C		0.028		Ω
Temperature coefficient of output voltage	IO = 5 mA		0°C to 125°C		-1.5		mV/°C
Output noise voltage	f = 10 Hz to 100 kHz		25°C		170		μV
Dropout voltage	I _O = 1 A		25°C		2		V
Bias current			25°C		4.6	8	mA
Diag ourrent change	V _I = 27 V to 38 V		0°C to 125°C			1	
Bias current change	$I_{O} = 5 \text{ mA to 1 A}$		0°C to 125°C	0.5		mA	
Short-circuit output current			25°C		150		mA
Peak output current			25°C		2.1		А



$\mu \text{A7800 SERIES} \\ \text{POSITIVE-VOLTAGE REGULATORS} \\$

SLVS056J - MAY 1976 - REVISED MAY 2003

APPLICATION INFORMATION




Figure 1. Fixed-Output Regulator





Figure 2. Positive Regulator in Negative Configuration (VI Must Float)






Figure 3. Adjustable-Output Regulator





Figure 4. Current Regulator



μA7800 SERIES POSITIVE-VOLTAGE REGULATORS

SLVS056J – MAY 1976 – REVISED MAY 2003



APPLICATION INFORMATION

Figure 5. Regulated Dual Supply

operation with a load common to a voltage of opposite polarity

In many cases, a regulator powers a load that is not connected to ground but, instead, is connected to a voltage source of opposite polarity (e.g., operational amplifiers, level-shifting circuits, etc.). In these cases, a clamp diode should be connected to the regulator output as shown in Figure 6. This protects the regulator from output polarity reversals during startup and short-circuit operation.




Figure 6. Output Polarity-Reversal-Protection Circuit

reverse-bias protection

Occasionally, the input voltage to the regulator can collapse faster than the output voltage. This can occur, for example, when the input supply is crowbarred during an output overvoltage condition. If the output voltage is greater than approximately 7 V, the emitter-base junction of the series-pass element (internal or external) could break down and be damaged. To prevent this, a diode shunt can be used as shown in Figure 7.





Figure 7. Reverse-Bias-Protection Circuit



MPFM001E - OCTOBER 1994 - REVISED JANUARY 2001

PowerFLEX[™] PLASTIC FLANGE-MOUNT




- NOTES: A. All linear dimensions are in inches (millimeters).
 - B. This drawing is subject to change without notice.
 - C. The center lead is in electrical contact with the thermal tab.
 - D. Dimensions do not include mold protrusions, not to exceed 0.006 (0,15).
 - E. Falls within JEDEC MO-169

KTE (R-PSFM-G3)

PowerFLEX is a trademark of Texas Instruments.

KCS (R-PSFM-T3)

PLASTIC FLANGE-MOUNT PACKAGE



NOTES:

- A. All linear dimensions are in inches (millimeters).B. This drawing is subject to change without notice.
- Lead dimensions are not controlled within this area.


D. All lead dimensions apply before solder dip.

- E. The center lead is in electrical contact with the mounting tab.
- \overbrace{F} The chamfer is optional.
- A Thermal pad contour optional within these dimensions.
- A Falls within JEDEC TO-220 variation AB, except minimum lead thickness.



KC (R-PSFM-T3)

PLASTIC FLANGE-MOUNT PACKAGE



NOTES:

- A. All linear dimensions are in inches (millimeters).B. This drawing is subject to change without notice.
- Lead dimensions are not controlled within this area.

D. All lead dimensions apply before solder dip.

- E. The center lead is in electrical contact with the mounting tab.
- \overbrace{F} The chamfer is optional.
- A Thermal pad contour optional within these dimensions.
- \triangle Falls within JEDEC TO-220 variation AB, except minimum lead thickness.



IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DSP	dsp.ti.com	Broadband	www.ti.com/broadband
Interface	interface.ti.com	Digital Control	www.ti.com/digitalcontrol
Logic	logic.ti.com	Military	www.ti.com/military
Power Mgmt	power.ti.com	Optical Networking	www.ti.com/opticalnetwork
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
		Telephony	www.ti.com/telephony
		Video & Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless

Mailing Address:

Texas Instruments

Post Office Box 655303 Dallas, Texas 75265

Copyright © 2004, Texas Instruments Incorporated