

Omnidirectional Microphone with Bottom Port and Analog Output

ADMP401

FEATURES

4.72 mm × 3.76 mm × 1.0 mm surface-mount package High SNR of 62 dBA Sensitivity of -42 dBV Flat frequency response from 100 Hz to 15 kHz Low current consumption of <250 μA Single-ended analog output High PSRR of 70 dB Compatible with Sn/Pb and Pb-free solder processes RoHS/WEEE compliant


APPLICATIONS

Smartphones and feature phones Digital video cameras Bluetooth headsets Video phones Teleconferencing systems

GENERAL DESCRIPTION

The ADMP401 is a high quality, low cost, low power analog output bottom-ported omnidirectional MEMS microphone. The ADMP401 consists of a MEMS microphone element, an impedance converter, and an output amplifier. The ADMP401 sensitivity specification makes it an excellent choice for both near field and far field applications. The ADMP401 has a high SNR and flat wideband frequency response, resulting in natural sound with high intelligibility. Low current consumption enables long battery life for portable applications. A built-in particle filter provides for high reliability. The ADMP401 complies with the TIA-920 standard *Telecommunications Telephone Terminal Equipment Transmission Requirements for Wideband Digital Wireline Telephones*.

The ADMP401 is available in a thin, $4.72 \text{ mm} \times 3.76 \text{ mm} \times 1.0 \text{ mm}$ surface-mount package. It is reflow solder compatible with no sensitivity degradation. The ADMP401 is halide free.



FUNCTIONAL BLOCK DIAGRAM

TABLE OF CONTENTS

Features	1
Applications	1
General Description	1
Functional Block Diagram	1
Revision History	2
Specifications	3
Absolute Maximum Ratings	4
ESD Caution	4
Pin Configuration and Function Descriptions	5
PCB Land Pattern Layout	6
Typical Performance Characteristics	7

Applications Information	8
Connecting the ADMP401 to a Codec	8
Connecting the ADMP401 to an Op Amp Gain Stage	8
Handling Instructions	9
Pick-and-Place Equipment	9
Reflow Solder	9
Board Wash	9
Reliability Specifications	10
Outline Dimensions	. 11
Ordering Guide	11

REVISION HISTORY

4/10—Revision 0: Initial Version

SPECIFICATIONS

T_A = 25°C, V_{DD} = 1.8 V, unless otherwise noted. All minimum and maximum specifications are guaranteed. Typical specifications are not guaranteed.

Table 1.

Parameter	Symbol	Test Conditions/Comments	Min	Тур	Max	Unit
PERFORMANCE						
Directionality				Omni		
Sensitivity		1 kHz, 94 dB SPL	-45	-42	-39	dBV
Signal-to-Noise Ratio	SNR			62		dBA
Equivalent Input Noise	EIN			32		dBA SP
Frequency Response ¹		Low frequency, –3 dB point		100		Hz
		High frequency, –3 dB point		15		kHz
		Deviation from flat response within pass band	-3		+2	dB
Total Harmonic Distortion	THD	105 dB SPL			3	%
Power Supply Rejection Ratio	PSRR	217 Hz, 100 mV p-p square wave superimposed on $V_{DD} = 1.8$ V		70		dB
Maximum Acoustic Input		Peak		120		dB SPL
POWER SUPPLY						
Supply Voltage	V _{DD}		1.5		3.3	V
Supply Current	ls				250	μΑ
OUTPUT CHARACTERISTICS						
Output Impedance	Zout			200		Ω
Output DC Offset				0.8		V
Output Current Limit				90		μA
Polarity				Noninvertir	ng²	

¹ See Figure 6 and Figure 7. ² Positive-going (increasing) pressure on the membrane results in a positive-going (increasing) output voltage.

ABSOLUTE MAXIMUM RATINGS

Table 2.

Parameter	Rating
Supply Voltage	3.6 V
Sound Pressure Level (SPL)	160 dB
Mechanical Shock	10,000 g
Vibration	Per MIL-STD-883 Method 2007, Test Condition B
Temperature Range	-40°C to +70°C

Stresses above those listed under Absolute Maximum Ratings may cause permanent damage to the device. This is a stress rating only; functional operation of the device at these or any other conditions above those indicated in the operational section of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

ESD CAUTION



ESD (electrostatic discharge) sensitive device. Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.




Table 3. Recommended Soldering Profile Limits

Profile Feature	Sn63/Pb37	Pb-Free
Average Ramp Rate (T_L to T_P)	3°C/sec max	3°C/sec max
Preheat		
Minimum Temperature (T _{SMIN})	100°C	150℃
Maximum Temperature (T _{SMAX})	150°C	200°C
Time (T _{SMIN} to T _{SMAX}), ts	60 sec to 120 sec	60 sec to 120 sec
Ramp-Up Rate (T _{SMAX} to T _L)	3°C/sec max	3°C/sec max
Time Maintained Above Liquidous (t _L)	60 sec to 150 sec	60 sec to 150 sec
Liquidous Temperature (T _L)	183℃	217°C
Peak Temperature (T _P)	240°C + 0°C/–5°C	260°C + 0°C/–5°C
Time Within 5°C of Actual Peak Temperature (t _P)	10 sec to 30 sec	20 sec to 40 sec
Ramp-Down Rate	6°C/sec max	6°C/sec max
Time 25°C to Peak Temperature	6 minute max	8 minute max

PIN CONFIGURATION AND FUNCTION DESCRIPTIONS




Figure 3. Pin Configuration (Bottom View)

Table 4. Pin Function Descriptions

Pin No.	Mnemonic	Description
1	OUTPUT	Analog Output Signal.
2	GND	Ground.
3	GND	Ground.
4	GND	Ground.
5	V _{DD}	Power Supply.
6	GND	Ground.

PCB LAND PATTERN LAYOUT

The recommended PCB land pattern for the ADMP401 should have a 1:1 ratio to the solder pads on the microphone package, as shown in Figure 4. Care should be taken to avoid applying solder paste to the sound hole in the PCB. A suggested solder paste stencil pattern layout is shown in Figure 5. The diameter of the sound hole in the PCB should be larger than the diameter of the sound port of the microphone. A minimum diameter of 0.5 mm is recommended.







Figure 4. PCB Land Pattern Layout (Dimensions Shown in mm)



TYPICAL PERFORMANCE CHARACTERISTICS








Figure 7. Typical Frequency Response (Measured)

APPLICATIONS INFORMATION

The ADMP401 output can be connected to a dedicated codec microphone input (see Figure 9) or to a high input impedance gain stage (see Figure 10). A 0.1 μ F ceramic capacitor (C1) placed close to the ADMP401 supply pin (V_{DD}) is used for testing and is recommended to adequately decouple the microphone from noise on the power supply. A 1 μ F or larger dc-blocking tantalum capacitor (C2) is required at the output of the microphone.

CONNECTING THE ADMP401 TO A CODEC




Figure 9. ADMP401 Connected to the ADAU1761 Codec

CONNECTING THE ADMP401 TO AN OP AMP GAIN STAGE




Figure 10. ADMP401 Connected to the OP177 Op Amp

HANDLING INSTRUCTIONS

PICK-AND-PLACE EQUIPMENT

The MEMS microphone can be handled using standard pickand-place and chip shooting equipment. Care should be taken to avoid damage to the MEMS microphone structure as follows:

- Use a standard pickup tool to handle the microphone. Because the microphone hole is on the bottom of the package, the pickup tool can make contact with any part of the lid surface.
- Use care during pick-and-place to ensure that no high shock events above 20 kg are experienced, because such events may cause damage to the microphone.
- Do not pick up the microphone with a vacuum tool that makes contact with the bottom side of the microphone. Do not pull air out or blow air into the microphone port.
- Do not use excessive force to place the microphone on the PCB.

REFLOW SOLDER

For best results, the soldering profile should be in accordance with the recommendations of the manufacturer of the solder paste that is used to attach the MEMS microphone to the PCB. It is recommended that the solder reflow profile not exceed the limit conditions specified in Figure 2 and Table 3.


BOARD WASH


When washing the PCB, ensure that water does not make contact with the microphone port. Blow-off procedures and ultrasonic cleaning must not be used.

RELIABILITY SPECIFICATIONS

The microphone sensitivity after stress must deviate by no more than ± 3 dB from the initial value.

Table 5.			
Stress Test	Description		
Low Temperature Operating Life	–40°C, 500 hours, powered		
High Temperature Operating Life	+125°C, 500 hours, powered		
ТНВ	+65°C/85% relative humidity, 500 hours, powered		
Temperature Cycle	–40°C/+125°C, one cycle per hour, 100 cycles		
High Temperature Storage	+150°C, 500 hours		
Low Temperature Storage	–40°C, 500 hours		
Component CDM ESD	All pins, 0.5 kV		
Component HBM ESD	All pins, 1.5 kV		
Component MM ESD	All pins, 0.2 kV		





ORDERING GUIDE

Model ¹	Temperature Range	Package Description	Package Option	Ordering Quantity
ADMP401ACEZ	-40°C to +70°C	6-Terminal LGA_CAV	CE-6-1 ²	1
ADMP401ACEZ-RL	-40°C to +70°C	6-Terminal LGA_CAV, 13"Tape and Reel	CE-6-1 ²	4,000
ADMP401ACEZ-RL7	-40°C to +70°C	6-Terminal LGA_CAV, 7"Tape and Reel	CE-6-1 ²	1,000
EVAL-ADMP401Z		Evaluation Board		

¹ Z = RoHS Compliant Part.

² This package option is halide free.

NOTES

©2010 Analog Devices, Inc. All rights reserved. Trademarks and registered trademarks are the property of their respective owners. D07712-0-4/10(0)



www.analog.com

Rev. 0 | Page 12 of 12