
### ULN2803A DARLINGTON TRANSISTOR ARRAY

SLRS049C - FEBRUARY1997 - REVISED AUGUST 2004

- 500-mA Rated Collector Current (Single Output)
- High-Voltage Outputs . . . 50 V
- Output Clamp Diodes
- Inputs Compatible With Various Types of Logic
- Relay Driver Applications
- Compatible with ULN2800A Series

#### description/ordering information

The ULN2803A is a high-voltage, high-current Darlington transistor array. The device consists of eight npn Darlington pairs that feature high-voltage outputs with common-cathode clamp diodes for switching inductive loads. The collector-current rating of each Darlington pair is 500 mA. The Darlington pairs may be connected in parallel for higher current capability.



Applications include relay drivers, hammer drivers, lamp drivers, display drivers (LED and gas discharge), line drivers, and logic buffers. The ULN2803A has a 2.7-k $\Omega$  series base resistor for each Darlington pair for operation directly with TTL or 5-V CMOS devices.

#### ORDERING INFORMATION

TA	PACKAGE <sup>†</sup>		ORDERABLE PART NUMBER	TOP-SIDE MARKING	
-40°C to 85°C	PDIP (N)	Tube of 20	ULN2803AN	ULN2803AN	
	SOIC (DW)	Tube of 40	ULN2803ADW	LIL NIGOGO A	
		Reel of 2000	ULN2003ADWR	ULN2803A	


<sup>†</sup> Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.




Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



#### logic diagram



# schematic (each Darlington pair)





SLRS049C - FEBRUARY1997 - REVISED AUGUST 2004

#### absolute maximum ratings at 25°C free-air temperature (unless otherwise noted)†

Collector-emitter voltage	50 V
Input voltage (see Note 1)	30 V
Continuous collector current	500 mA
Output clamp diode current	500 mA
Total substrate-terminal current	–2.5 A
Package thermal impedance, θ <sub>JA</sub> (see Notes 2 and 3): DW package	$\dots \dots  TBD^{\circ}C/W$
N package	TBD°C/W
Operating virtual junction temperature, T <sub>J</sub>	150°C
Storage temperature range, T <sub>stg</sub>	$\dots$ -65°C to 150°C

<sup>†</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- NOTES: 1. All voltage values, unless otherwise noted, are with respect to the emitter/substrate terminal GND.
  - 2. Maximum power dissipation is a function of  $T_J(max)$ ,  $\theta_{JA}$ , and  $T_A$ . The maximum allowable power dissipation at any allowable ambient temperature is  $P_D = (T_J(max) T_A)/\theta_{JA}$ . Operating at the absolute maximum  $T_J$  of 150°C can affect reliability.
  - 3. The package thermal impedance is calculated in accordance with JESD 51-7.

#### electrical characteristics at 25°C free-air temperature (unless otherwise noted)

PARAMETER		TEST CONDITIONS		MIN	TYP	MAX	UNIT
ICEX	Collector cutoff current	V <sub>CE</sub> = 50 V, See Figure 1	$I_{\parallel} = 0$ ,			50	μΑ
I <sub>I(off)</sub>	Off-state input current	V <sub>CE</sub> = 50 V, T <sub>A</sub> = 70°C,	$I_C = 500 \mu A$ , See Figure 2	50	65		μΑ
I <sub>I(on)</sub>	Input current	V <sub>I</sub> = 3.85 V,	See Figure 3		0.93	1.35	mA
	On-state input voltage	V <sub>CE</sub> = 2 V, See Figure 4	$I_C = 200 \text{ mA}$			2.4	V
V <sub>I(on)</sub>			$I_C = 250 \text{ mA}$			2.7	
			$I_C = 300 \text{ mA}$			3	
VCE(sat)	Collector-emitter saturation voltage	I <sub>I</sub> = 250 μA, See Figure 5	$I_C = 100 \text{ mA},$		0.9	1.1	
		I <sub>I</sub> = 350 μA, See Figure 5	$I_C = 200 \text{ mA},$		1	1.3	V
		I <sub>I</sub> = 500 μA, See Figure 5	$I_C = 350 \text{ mA},$		1.3	1.6	
I <sub>R</sub>	Clamp diode reverse current	$V_{R} = 50 V$ ,	See Figure 6			50	μΑ
٧F	Clamp diode forward voltage	I <sub>F</sub> = 350 mA,	See Figure 7		1.7	2	V
Ci	Input capacitance	V <sub>I</sub> = 0 V,	f = 1 MHz		15	25	pF

#### switching characteristics at 25°C free-air temperature

PARAMETER		TEST CONDITIONS		MIN	TYP	MAX	UNIT
tPLH	Propagation delay time, low- to high-level output	$V_S = 50 \text{ V},$	$R_{L} = 163  \Omega$ ,		130		
tPHL	Propagation delay time, high- to low-level output	$C_L = 15 pF,$	See Figure 8		20		ns
Vон	High-level output voltage after switching	V <sub>S</sub> = 50 V, See Figure 9	$I_O \approx 300 \text{ mA},$	V <sub>S</sub> - 20			mV



#### PARAMETER MEASUREMENT INFORMATION




Figure 1. I<sub>CEX</sub> Test Circuit




Figure 2. I<sub>I(off)</sub> Test Circuit




Figure 3. I<sub>I(on)</sub> Test Circuit




Figure 4. V<sub>I(on)</sub> Test Circuit




Figure 5.  $h_{FE}$ ,  $V_{CE(sat)}$  Test Circuit




Figure 6. I<sub>R</sub> Test Circuit

#### PARAMETER MEASUREMENT INFORMATION






Figure 7. V<sub>F</sub> Test Circuit



**Test Circuit** 




**Voltage Waveforms** 

NOTES: A. The pulse generator has the following characteristics: PRR = 1 MHz,  $Z_O$  = 50  $\Omega$ . B.  $C_L$  includes probe and jig capacitance.


- C. V<sub>IH</sub> = 3 V

Figure 8. Propagation Delay Times

### PARAMETER MEASUREMENT INFORMATION



**Test Circuit** 



**Voltage Waveforms** 

NOTES: A. The pulse generator has the following characteristics: PRR = 12.5 KHz,  $Z_O$  = 50  $\Omega$ .


- B. C<sub>L</sub> includes probe and jig capacitance.
  C. V<sub>IH</sub> = 3 V

Figure 9. Latch-Up Test



# DW (R-PDSO-G18)

## PLASTIC SMALL-OUTLINE PACKAGE



NOTES:


- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15).
- D. Falls within JEDEC MS-013 variation AB.



# N (R-PDIP-T\*\*)

## PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- The 20 pin end lead shoulder width is a vendor option, either half or full width.



#### **IMPORTANT NOTICE**

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DSP	dsp.ti.com	Broadband	www.ti.com/broadband
Interface	interface.ti.com	Digital Control	www.ti.com/digitalcontrol
Logic	logic.ti.com	Military	www.ti.com/military
Power Mgmt	power.ti.com	Optical Networking	www.ti.com/opticalnetwork
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
		Telephony	www.ti.com/telephony
		Video & Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless

Mailing Address: Texas Instruments

Post Office Box 655303 Dallas, Texas 75265

Copyright © 2004, Texas Instruments Incorporated