


**Model name: LM-103-D6**  
**532nm Green Laser Module**

1. Specification:

- . Wavelength: ..... 532nm
- . Output power: ..... < 5mW ( FDA class IIIa)
- . Output mode: ..... CW
- . Beam size: ..... < 6.5mm at 5M distance. (at 25 °C).
- . Input Power Source: ..... DC2.5V ~4.5V
- . Consumption Current: ..... Max: 300mA
- . Life Time: ..... 3000 hours
- . Operating Temperature ..... 15 °C ~35 °C
- . Dimension: ..... 11 mm x 56 mm(L)

2. Dimension:



unit: mm



**WEN TAI ENTERPRISE CO.,LTD**

**ADDRESS:** 6F-3, No.123, Lane 235, Pao-Chiao Road, Shintien city, Taipei Hsien, Taiwan, R.O.C  
**TEL:** 886-2-89192318 **FAX:** 886-2-89192320 [Http://www.a-wentai.com](http://www.a-wentai.com)